



Halogen non-reflector

7748XHP 250W G6.35 24V 1CT/10X10F

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.


Product data

General information	
Cap base	G6.35 [G6.35]
Philips code	7748XHP
ANSI Code	EHJ
LIF Code	A1/223
Operating position	S90 [Standing +/-90D or Base Down (BDH)]
Main application	Projection
Life to 50% failures (nom.)	50 h
Light technical	
Luminous flux (rated) (nom.)	10000 lm
Correlated Colour Temperature (Nom)	3550 K
Colour rendering index (nom.)	100
Operating and electrical	
Power (Rated) (Nom)	250 W
Voltage (Nom)	24 V

Mechanical and housing	
Bulb material	Quartz-UV Open
Filament shape	Flat
Filament dimensions WxH	7.0x3.5
Luminaire design requirements	
Bulb temperature (max.)	900 °C
Pinch temperature (max.)	400 °C
Product data	
Full product code	871150041029050
Order product name	7748XHP EHJ-S 250W G6.35 24V
EAN/UPC – product	8711500410290
Order code	41029050
SAP numerator – quantity per pack	1
Numerator – packs per outer box	100
SAP material	924006520503
Copy Net Weight (Piece)	0.004 kg

Halogen non-reflector

Dimensional drawing



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
7748XHP	12.5 mm	32.75	33.25	33	1.05 mm	1 mm	0.95	55 mm
EHJ-S 250W G6.35 24V		mm	mm	mm			mm	

7748XHP EHJ-S 250W G6.35 24V

