



Halogen reflector

13629 150W GX5.3 21V 1CT/24

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.


产品数据

一般信息	
底盖	GX5.3 [GX5.3]
操作位置	S90 [直立 +/-90D 或底座朝下 (BDH)]
50% 故障条件下的使用寿命 (标称)	200 小时
灯技术	
显色指数 (CRI)	100
操作和电气	
功耗	150 W
电压 (标称)	21 V
电压 (标称)	21 V
控制和调光	
可调光	是

机械和外壳	
灯泡材料	开放紫外线石英
反射器外观	光滑
产品数据	
订单产品名称	13629 150W GX5.3 21V 1CT/24
完整的产品名称	13629 150W GX5.3 21V 1CT/24
完整产品代码	871150041073330
订购代码	924010319894
材料编号 (12NC)	924010319894
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500410733
计算器 - 每个外包装箱中的包数	24
EAN/UPC - 案例	8711500421616

Halogen reflector

二维绘图



Product	D (max)	C (max)
13629 150W GX5.3 21V 1CT/24	50.7 mm	44.5 mm

