



Halogen non-reflector

7158XHP 150W G6.35 24V 1CT/10X10F

Low-voltage quartz halogen capsule lamps

Product data

| General Information | |
|------------------------------------|--|
| Cap-Base | G6.35 [G6.35] |
| Operating Position | S90 [Standing +/-90D or Base Down (BDH)] |
| Life to 50% Failures (Nom) | 40 hour(s) |
| Light Technical | |
| Correlated Color Temperature (Nom) | 3450 K |
| Color rendering index (CRI) | 100 |
| Operating and Electrical | |
| Power Consumption | 150 W |
| Voltage (Nom) | 24 V |
| Voltage (Nom) | 24 V |
| Mechanical and Housing | |
| Bulb Material | Quartz-UV Open |

| Product Data | |
|---------------------------------|-----------------------------------|
| Order product name | 7158XHP 150W G6.35 24V 1CT/10X10F |
| Full product name | 7158XHP 150W G6.35 24V 1CT/10X10F |
| Full product code | 871150041020750 |
| Order code | 924031720503 |
| Material Nr. (12NC) | 924031720503 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500410207 |
| Numerator - Packs per outer box | 100 |
| EAN/UPC - Case | 8711500423221 |

Halogen non-reflector

Dimensional drawing



| Product | D (max) | L (min) | L (max) | L | P (max) | P | P (min) | C (max) |
|--------------|---------|---------|---------|----|---------|------|---------|---------|
| 7158XHP 150W | 11.5 mm | 31.5 mm | 33.25 | 33 | 1.05 mm | 1 mm | 0.95 | 50 mm |
| G6.35 24V | | | mm | mm | | | mm | |
| 1CT/10X10F | | | | | | | | |

