



Capsuleline

Caps 20W GY6.35 12V CL 4000h 1CT/10X10F


Low-voltage halogen capsule. Ideal solution for small decorative luminaires. UV-block glass and low-pressure filling allow usage without cover glass. The compact Capsuleline delivers crisp white light over a long lifetime.

Product data

General Information	
Cap-Base	GY6.35 [GY6.35]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	4,000 hour(s)
Switching Cycle	16,000
Rated Lifetime (Hours)	4,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	300 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	15 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	20.0 W
Lamp Current (Nom)	1.66 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	12 V
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T11 [T 11mm]
Approval and Application	
Energy Consumption kWh/1000 h	21 kWh
Product Data	
Order product name	Caps 20W GY6.35 12V CL 4000h 1CT/10X10F
Full product name	Caps 20W GY6.35 12V CL 4000h 1CT/10X10F
Full product code	871150040219650
Order code	924040417101
Material Nr. (12NC)	924040417101
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500402196
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500425782

Dimensional drawing



Product	D (max)	L	C (max)
Caps 20W GY6.35 12V CL 4000h 1CT/10X10F	12 mm	30 mm	44 mm

