



Halogen non-reflector

EYB 82V 360W 24PK

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.


Product data

General Information	
Cap-Base	G5.3 [G5.3]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	75 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3300 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	360 W
Voltage (Nom)	82 V
Voltage (Nom)	82 V
Mechanical and Housing	
Bulb Material	Quartz-UV Open

Product Data	
Order product name	14531 360W G5.3 82V 1CT
Full product name	EYB 82V 360W 24PK
Full product code	871150042463130
Order code	232579
Material Nr. (12NC)	924041528894
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500424631
Numerator - Packs per outer box	24
EAN/UPC - Case	8711500424648

Halogen non-reflector

Dimensional drawing



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
14531 360W	11.5 mm	30.8 mm	32 mm	31.8	1.65 mm	1.50	1.47 mm	57 mm
G5.3 82V 1CT				mm		mm		

