



# MR16

## 20MR16/FL36 BAB 50PK

Philips Halogen MR16 lamps provide a bright white light for accent lighting. They make it easy to optimize the look and feel of your brand, your merchandise, and the shoppers experience, with lower operating costs.

### Product data

General Information	
Base	GU5.3 [ GU5.3]
Philips Code	14592
Operating Position	Universal [ Universal]
ANSI Code Halogen	BAB
Nominal Lifetime (Nom)	3000 h

  

Light Technical	
Beam Angle (Nom)	36 °
Luminous Intensity (Max)	550 cd
Rated Beam Angle	36 °
Correlated Color Temperature (Nom)	3000 K
Color Rendering Index (Nom)	100

  

Operating and Electrical	
Power (Rated) (Nom)	20.0 W
Lamp Current (Nom)	1.67 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	12 V

  

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy Efficiency Label (EEL)	Not applicable

  

Luminaire Design Requirements	
Bulb Temperature (Max)	250 °C
Cap-Base Temperature (Max)	350 °C

  

Product Data	
Order product name	20MR16/FL36 BAB 50PK
EAN/UPC - Product	046677378035
Order code	378034
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	50
Material Nr. (12NC)	924047217122
Net Weight (Piece)	0.032 kg
ILCOS Code	HRGI-20-12-GU5.3-50/36

## MR16

### Dimensional drawing



Fighter 14592 20W GU5.3 12V MR16 36D

Product	D (max)	C (max)
20MR16/FL36 BAB 50PK	51 mm	46 mm

