



Long Life MR-16

EXZ 50W GU5.3 12V MR16 24D CL 1CT/10X5F

Philips Halogen Long Life MR16 lamps make it easy to optimize the look and feel of your brand, your merchandise, and the shoppers experience, with lower operating costs.

Warnings and Safety

- CAUTION: THIS LAMP IS PRESSURIZED AND COULD SHATTER so to avoid injury and to avoid exposure to ultraviolet radiation, this lamp should be used in a fixture that provides a protective shield of tempered glass. Provide adequate ventilation to ensure that seal temperature does not exceed 350 degrees C and use only in fixtures rated for the wattage stated on this package. To avoid risks of burns or other injury, turn power off and allow lamp to fully cool before attempting to replace. Socket condition may affect lamp life. Inspect and replace socket if deterioration has occurred.

Product data


General Information		Starting Time (Nom)		0.0 s
Cap-Base	GU5.3 [GU5.3]	Warm-up time to 60% light		instant full light s
Operating Position	UNIVERSAL [Any or Universal (U)]	Power Factor (Fraction)		1
Nominal lifetime	4,000 hour(s)	Voltage (Nom)		12 V
Switching Cycle	16,000	Voltage (Nom)		12 V
Rated Lifetime (Hours)	4,000 hour(s)			
Lighting Technology	Halogen	Controls and Dimming		
		Dimmable		Yes
Light Technical		Mechanical and Housing		
Beam Angle (Nom)	24 degree(s)	Bulb Finish		Clear
Correlated Color Temperature (Nom)	3000 K	Bulb Shape		MR16 [2inch/50mm]
Color rendering index (CRI)	100			
Luminous Flux in 90° Cone (Rated)	775 lumen	Approval and Application		
Operating and Electrical		Energy Consumption kWh/1000 h		53 kWh
Power Consumption	50.0 W			
Lamp Current (Nom)	4.2 A			

Long Life MR-16

Product Data	
Full product code	904667737817260
Order product name	EXZ 50W GU5.3 12V MR16 24D CL 1CT/10X5F
Order code	924050917130
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	50


Material Nr. (12NC)	924050917130
Full product name	EXZ 50W GU5.3 12V MR16 24D CL 1CT/10X5F
EAN/UPC - Case	50046677378177
EAN/UPC - Product/Case	046677378172

Dimensional drawing



Product	D (max)	C (max)
EXZ 50W GU5.3 12V MR16 24D CL 1CT/10X5F	51 mm	46 mm

Photometric data



Light Distribution Diagram - EXZ 50W GU5.3 12V MR16 24D CL 1CT/10X5F

