



MASTERLine 111

MASTERLINE 111 45W G53 12V 45D 1CT/6

Low-voltage halogen reflector lamp with double-ended burner and high-purity aluminium reflector


Product data

General Information	
Cap base	G53 [G53]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	4,000 h
Switching Cycle	16,000
Rated Lifetime (Hours)	4,000 h
Lighting Technology	Halogen
Light Technical	
Beam angle (nom.)	45 degree(s)
Correlated Colour Temperature	3000 K
Colour rendering index (CRI)	100
Luminous flux in 90° cone (rated)	640 lm
Operating and Electrical	
Power Consumption	45.0 W
Lamp current (nom.)	3.8 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light	Instant full light s
Power Factor (Fraction)	1
Voltage (nom.)	12 V
Voltage (nom.)	12 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb shape	R111 [R 111 mm]
Approval and Application	
Energy consumption kWh/1,000 hours	48 kWh
Product Data	
Order product name	MASTERLine 111 45W G53 12V 45D 1CT/6
Full product name	MASTERLINE 111 45W G53 12V 45D 1CT/6
Full EOC	871150041109910
Order code	41109910
Material no. (12 NC)	924058817161
Local order code	45ML11145D
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500411099
Numerator – packs per outer box	6
EAN/UPC – Case	8711500437358


MASTERLine 111

Dimensional drawing



Product	D (max)	C (max)	C1 (max)
MASTERLine 111 45W G53 12V 45D 1CT/6	111 mm	67 mm	51 mm

Photometric data



Light Distribution Diagram - MASTERLine 111 45W G53 12V 45D 1CT/6

