



Appliance Sewing Machine Tubular

Appliance 20W B15d 230V T22X51 CL SM 1CT

Tubular incandescent vacuum lamp

Product data

General Information	
Cap-Base	B15 [B15]
Operating Position	UNIVERSAL [Any or Universal (U)]
Main Application	Sewing Machine
Nominal Lifetime (Nom)	1000 h
Switching Cycle	4000X

Light Technical	
Luminous Flux (Nom)	120 lm
Luminous Flux (Rated) (Nom)	120 lm
Colour Temperature, horizontal (Nom)	2700 K
Colour Rendering Index horiz (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	20.0 W
Lamp Current (Nom)	0.09 A
Starting Time (Nom)	0.0 s
Warm Up Time to 60% Light (Nom)	instant full light
Power Factor (Nom)	1
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Clear (CL)

Approval and Application	
Energy Efficiency Label	E
Energy Consumption kWh/1000 h	20 kWh

Product Data	
Full product code	871150025023050
Order product name	Appliance 20W B15d 230V T22X51 - CL SM - 1CT
EAN/UPC - Product	8711500250230
Order code	25023050
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material Nr. (12NC)	924132044240
Net Weight (Piece)	10.850 g
ILCOS Code	N/A

Appliance Sewing Machine Tubular

Dimensional drawing



Product	D (max)	C (max)
Appliance 20W B15d 230V T22X51 - CL SM - 1CT	22 mm	52 mm

APP 20W B15d 230V T22X51 CL SM

