



Deco Tubular

Deco 7W E14 230-240V T17 CL 1CT/10X10F

Tubular lamps with single- and coiled-coil filaments and clear, inside frosted or internally coated white bulbs with B- or E-base


Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal Lifetime (Nom)	1000 h
Switching Cycle	4000X
Light Technical	
Luminous Flux (Nom)	21 lm
Luminous Flux (Rated) (Nom)	21 lm
Colour Temperature, horizontal (Nom)	2700 K
Colour Rendering Index horiz (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	7 W
Lamp Current (Nom)	0.03 A
Starting Time (Nom)	0.0 s
Warm Up Time to 60% Light (Nom)	instant full light
Power Factor (Nom)	1
Voltage (Nom)	230-240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear (CL)
Approval and Application	
Energy Efficiency Label	E
Energy Consumption kWh/1000 h	7 kWh
Product Data	
Full product code	871150025008750
Order product name	Deco 7W E14 230-240V T17 CL 1CT/10X10F
EAN/UPC - Product	8711500250087
Order code	25008750
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material Nr. (12NC)	924151144440
Net Weight (Piece)	8.000 g
ILCOS Code	N/A

Deco Tubular

Dimensional drawing



Product	D (max)	C (max)
Deco 7W E14 230-240V T17 CL 1CT/10X10F	17 mm	54 mm

TUB 7W E14 230-240V T17 CL

