



Deco Tubular

DECO 10W E14 240-250V T17 CL 1CT/10X10F

Tubular lamps with single- and coiled-coil filaments and clear, inside frosted or internally coated white bulbs with B- or E-base


Product data

| General Information | |
|------------------------------------|----------------------------------|
| Cap-Base | E14 |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 1,000 hour(s) |
| Switching Cycle | 4,000 |
| Rated Lifetime (Hours) | 1,000 hour(s) |
| Lighting Technology | Incandescent |
| Light Technical | |
| Luminous Flux | 37 lm |
| Correlated Color Temperature (Nom) | 2700 K |
| Color rendering index (CRI) | 100 |
| Operating and Electrical | |
| Power Consumption | 10.0 W |
| Starting Time (Nom) | 0.0 s |
| Warm-up time to 60% light | instant full light s |
| Power Factor (Fraction) | 1 |
| Voltage (Nom) | 240-250 V |
| Controls and Dimming | |
| Dimmable | Yes |

| Mechanical and Housing | |
|---------------------------------|---|
| Bulb Finish | Clear |
| Bulb Shape | T17 |
| Approval and Application | |
| Energy Consumption kWh/1000 h | 10 kWh |
| Product Data | |
| Order product name | Deco 10W E14 240-250V T17 CL 1CT/10X10F |
| Full product name | DECO 10W E14 240-250V T17 CL 1CT/10X10F |
| Full product code | 871150003821050 |
| Order code | 03821050 |
| Material Nr. (12NC) | 924151445740 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500038210 |
| Numerator - Packs per outer box | 100 |
| EAN/UPC - Case | 8711500251657 |

Deco Tubular

Dimensional drawing



| Product | D (max) | C (max) |
|---|---------|---------|
| Deco 10W E14 240-250V T17 CL 1CT/10X10F | 17 mm | 54 mm |

