



Appliance Oven Tubular

Appliance 15W E14 230-240V T22 CL OV 1CT

Tubular vacuum lamps with clear glass (T-bulb)

Product data

General Information	
Cap base	E14 [E14]
Burning Position	UNIVERSAL [Any/Universal]
Main application	Oven
Nominal lifetime (nom.)	1000 h
Switching cycle	4000X

Light Technical	
Lamp Luminous Flux 25°C EL (Nom)	90 lm
Lamp Luminous Flux (Nom)	90 lm
Colour Temperature, horizontal (Nom)	2700 K
Colour Rendering Index,horiz (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	15.0 W
Lamp current (nom.)	0.06 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1
Voltage (Nom)	230-240 V

Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Bulb finish	Clear (CL)


Approval and Application	
Energy efficiency label (EEL)	E
Energy Consumption kWh/1000 h	15 kWh

Product Data	
Full product code	871150003659950
Order product name	Appliance 15W E14 230-240V T22 CL OV 1CT
EAN/UPC – product	8711500036599
Order code	924196244440
Local Code	OVEN15W235VSES
Numerator – quantity per pack	1
Numerator – packs per outer box	100
Material no. (12NC)	924196244440
Net weight (piece)	10.500 g
ILCOS Code	IBT/C-15-230/240-E14-22*

Appliance Oven Tubular

Dimensional drawing

Product	D (max)	C (max)
Appliance 15W E14 230-240V T22 CL OV 1CT	22 mm	49 mm



APP 15W E14 230-240V T22 CL OV

