



Appliance Oven Tubular

Appliance 15W E14 230-240V T22CL OV 1CT/20F/NO

Tubular vacuum lamps with clear glass (T-bulb)

Product data

General Information	
Cap base	E14 [E14]
Operating position	UNIVERSAL [Any or Universal (U)]
Main application	Oven
Nominal lifetime (nom.)	1000 h
Switching cycle	4.000X
Rated lifetime (hours)	1000 h
	Sphere
Light Technical	
Luminous flux (nom.)	85 lm
Luminous flux (rated) (nom.)	90 lm
Chromaticity coordinate X (nom.)	0.46
Chromaticity coordinate Y (nom.)	0.411
Correlated Colour Temperature (Nom)	2700 K
Colour rendering index (nom.)	100
Operating and Electrical	
Power (Rated) (Nom)	15.4 W
Lamp current (nom.)	0.06 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light

Power factor (nom.)	1
Voltage (Nom)	230-240 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T22 [T 22mm]
Approval and Application	
Energy Efficiency Class	G
Energy consumption kWh/1,000 hours	16 kWh
	423229
Product Data	
Full product code	871150003659905
Order product name	Appliance 15W E14 230-240V T22CL OV 1CT/20F/NO
EAN/UPC – product	8711500036599
Order code	03659905
SAP numerator – quantity per pack	1


Appliance Oven Tubular

Numerator – packs per outer box	20
SAP material	924196244442
SAP net weight (piece)	10.500 g

ILCOS code	IBT/C-15-230/240-E14-22*
------------	--------------------------

Dimensional drawing

Product	D (max)	C (max)
Appliance 15W E14 230–240V T22CL OV 1CT/20F/NO	22 mm	49 mm



APP 15W E14 230-240V T22 CL OV

