



Appliance Oven Tubular

App 15W E14 230-240V T22CL OV 1CT/20F/NO

Tubular vacuum lamps with clear glass (T-bulb)

Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Flux measurement reference	Sphere

Light Technical

Luminous Flux	85 lm
Chromaticity Coordinate X (Nom)	0.46
Chromaticity Coordinate Y (Nom)	0.411
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100

Operating and Electrical

Power Consumption	15.4 W
Lamp Current (Nom)	0.06 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1

Voltage (Nom)	230-240 V
---------------	-----------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	T22 [T 22mm]

Approval and Application

Energy Efficiency Class	G
Energy Consumption kWh/1000 h	16 kWh
EPREL Registration Number	423229

Product Data

Order product name	App 15W E14 230-240V T22CL OV 1CT/20F/NO
Full product name	App 15W E14 230-240V T22CL OV 1CT/20F/NO
Full product code	871150003659905
Order code	924196244442
Material Nr. (12NC)	924196244442
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500036599
Numerator - Packs per outer box	20

Appliance Oven Tubular

EAN/UPC - Case	8727900800678
----------------	---------------

Dimensional drawing

Product	D (max)	C (max)
App 15W E14 230-240V T22CL OV 1CT/20F/NO	22 mm	49 mm

