



Appliance Refrigerator Tubular

APPL 15W E14 230-240V T25 CL RF 2BL/10

Tubular lamp with clear glass bulb

Product data

General Information	
Cap base	E14 [E14]
Operating position	UNIVERSAL [Any/Universal]
Main application	Refrigerator
Nominal lifetime (nom.)	1000 h
Switching cycle	4000X

Light Technical	
Luminous flux (nom.)	110 lm
Luminous flux (rated) (nom.)	110 lm
Correlated colour temperature (nom.)	2700 K
Color rendering index (nom.)	100

Operating and Electrical	
Power (Rated) (Nom)	15.0 W
Lamp current (nom.)	0.06 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1
Voltage (Nom)	230-240 V

Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Bulb finish	Clear (CL)

Approval and Application	
Energy efficiency label (EEL)	E
Energy Consumption kWh/1000 h	15 kWh

Product Data	
Full product code	871150025024725
Order product name	Appliance 15W E14 230-240V T25 CL RF 2BL/10
EAN/UPC – product	8711500259837
Order code	25024725
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	924197744452
Net weight (piece)	12.500 g
ILCOS Code	IBT/C-15-230/240-E14-25*

Appliance Refrigerator Tubular

Dimensional drawing

Product	D (max)	C (max)
Appliance 15W E14 230-240V T25 CL RF 2BL/10	25 mm	57 mm



APP 15W E14 230-240V T25 CL RF

