



Appliance Oven Tubular

App 25W E14 230-240V T25 OV 1CT/10x10F

Tubular vacuum lamps with clear glass (T-bulb)

Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Luminous Flux	172 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	25.0 W
Lamp Current (Nom)	0.11 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230-240 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T25 [T 25mm]

Approval and Application	
Energy Consumption kWh/1000 h	25 kWh

Product Data	
Order product name	App 25W E14 230-240V T25 OV 1CT/10x10F
Full product name	App 25W E14 230-240V T25 OV 1CT/10x10F
Full product code	871869646676600
Order code	924198244403
Material Nr. (12NC)	924198244403
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696466766
Numerator - Packs per outer box	100
EAN/UPC - Case	8718696466780

Appliance Oven Tubular

Dimensional drawing

Product	D (max)	C (max)
App 25W E14 230-240V T25 OV 1CT/10x10F	25 mm	57 mm

