



# Appliance Oven Tubular

## APP 25W E14 230-240V T25 CL OV 1CT

Tubular vacuum lamps with clear glass (T-bulb)

### Product data

General Information	
Cap-Base	E14 [ E14]
Operating Position	UNIVERSAL [ Any or Universal (U)]
Main Application	Oven
Nominal Lifetime (Nom)	1000 h
Switching Cycle	4000X

  

Light Technical	
Luminous Flux (Nom)	172 lm
Luminous Flux (Rated) (Nom)	172 lm
Colour Temperature, horizontal (Nom)	2700 K
Colour Rendering Index horiz (Nom)	100

  

Operating and Electrical	
Power (Rated) (Nom)	25.0 W
Lamp Current (Nom)	0.11 A
Starting Time (Nom)	0.0 s
Warm Up Time to 60% Light (Nom)	instant full light
Power Factor (Nom)	1
Voltage (Nom)	230-240 V

  

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear (CL)

  

Approval and Application	
Energy Efficiency Label	E
Energy Consumption kWh/1000 h	25 kWh

  

Product Data	
Full product code	871150003871550
Order product name	Appliance 25W E14 230-240V T25 CL OV 1CT
EAN/UPC - Product	8711500038715
Order code	03871550
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material Nr. (12NC)	924198244440
Net Weight (Piece)	10.500 g
ILCOS Code	IBT/C-25-230/240-E14-25*

## Appliance Oven Tubular

### Dimensional drawing

Product	D (max)	C (max)
Appliance 25W E14 230-240V T25 CL OV 1CT	25 mm	57 mm



APP 25W E14 230-240V T25 CL OV

