



Appliance Oven Tubular

APP 25W E14 230-240V T25 CL OV 1CT

Tubular vacuum lamps with clear glass (T-bulb)

Product data

| General Information | |
|----------------------------|----------------------------------|
| Cap-Base | E14 [E14] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 1,000 hour(s) |
| Switching Cycle | 4,000 |
| Rated Lifetime (Hours) | 1,000 hour(s) |
| Lighting Technology | Incandescent |
| Flux measurement reference | Sphere |

Light Technical

| | |
|------------------------------------|--------|
| Luminous Flux | 165 lm |
| Chromaticity Coordinate X (Nom) | 0.46 |
| Chromaticity Coordinate Y (Nom) | 0.411 |
| Correlated Color Temperature (Nom) | 2700 K |
| Color rendering index (CRI) | 100 |

Operating and Electrical

| | |
|---------------------------|----------------------|
| Power Consumption | 26 W |
| Lamp Current (Nom) | 0.11 A |
| Starting Time (Nom) | 0.0 s |
| Warm-up time to 60% light | instant full light s |
| Power Factor (Fraction) | 1 |

| | |
|---------------|-----------|
| Voltage (Nom) | 230-240 V |
|---------------|-----------|

Controls and Dimming

| | |
|----------|-----|
| Dimmable | Yes |
|----------|-----|

Mechanical and Housing

| | |
|-------------|--------------|
| Bulb Finish | Clear |
| Bulb Shape | T25 [T 25mm] |

Approval and Application

| | |
|-------------------------------|--------|
| Energy Efficiency Class | G |
| Energy Consumption kWh/1000 h | 26 kWh |
| EPREL Registration Number | 423232 |

Product Data

| | |
|---------------------------------|------------------------------------|
| Order product name | App 25W E14 230-240V T25 CL OV 1CT |
| Full product name | APP 25W E14 230-240V T25 CL OV 1CT |
| Full product code | 871150003871550 |
| Order code | 03871550 |
| Material Nr. (12NC) | 924198244440 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500038715 |
| Numerator - Packs per outer box | 100 |

Appliance Oven Tubular

| | |
|----------------|---------------|
| EAN/UPC - Case | 8711500257918 |
|----------------|---------------|

Dimensional drawing

| Product | D (max) | C (max) |
|------------------------------------|---------|---------|
| App 25W E14 230-240V T25 CL OV 1CT | 25 mm | 57 mm |

