



# Appliance Oven Tubular

## Appliance 25W E14 230-240V T25CL OV 1CT/20F/NO

Tubular vacuum lamps with clear glass (T-bulb)

### Product data


General Information	
Cap base	E14 [ E14]
Operating position	UNIVERSAL [ Any or Universal (U)]
Main application	Oven
Nominal lifetime (nom.)	1000 h
Switching cycle	4000X
Light Technical	
Luminous flux (nom.)	172 lm
Luminous flux (rated) (nom.)	172 lm
Correlated colour temperature (nom.)	2700 K
Color rendering index (nom.)	100
Operating and Electrical	
Power (Rated) (Nom)	25.0 W
Lamp current (nom.)	0.11 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1
Voltage (Nom)	230-240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb finish	Clear (CL)
Approval and Application	
Energy efficiency label (EEL)	E
Energy Consumption kWh/1000 h	25 kWh
Product Data	
Full product code	871150003871505
Order product name	Appliance 25W E14 230-240V T25CL OV 1CT/20F/NO
EAN/UPC – product	8711500038715
Order code	03871505
Numerator – quantity per pack	1
Numerator – packs per outer box	20
Material no. (12NC)	924198244442
Net weight (piece)	10.500 g
ILCOS Code	IBT/C-25-230/240-E14-25*

## Appliance Oven Tubular

### Dimensional drawing

Product	D (max)	C (max)
Appliance 25W E14 230-240V T25CL OV 1CT/20F/NO	25 mm	57 mm



APP 25W E14 230-240V T25 CL OV

