



Appliance Oven Tubular

Appliance 25W E14 230-240V T25CL OV 1CT/20F/NO

Tubular vacuum lamps with clear glass (T-bulb)

Product data

General Information	
Cap base	E14 [E14]
Operating position	UNIVERSAL [Any or Universal (U)]
Main application	Oven
Nominal lifetime (nom.)	1000 h
Switching cycle	4.000X
Rated lifetime (hours)	1000 h
	Sphere
Light Technical	
Luminous flux (nom.)	165 lm
Luminous flux (rated) (nom.)	172 lm
Chromaticity coordinate X (nom.)	0.46
Chromaticity coordinate Y (nom.)	0.411
Correlated Colour Temperature (Nom)	2700 K
Colour rendering index (nom.)	100
Operating and Electrical	
Power (Rated) (Nom)	26 W
Lamp current (nom.)	0.11 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light

Power factor (nom.)	1
Voltage (Nom)	230-240 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T25 [T 25mm]
Approval and Application	
Energy Efficiency Class	G
Energy consumption kWh/1,000 hours	26 kWh
	423232
Product Data	
Full product code	871150003871505
Order product name	Appliance 25W E14 230-240V T25CL OV 1CT/20F/NO
EAN/UPC – product	8711500038715
Order code	03871505
SAP numerator – quantity per pack	1


Appliance Oven Tubular

Numerator – packs per outer box	20
SAP material	924198244442
SAP net weight (piece)	10.500 g

ILCOS code	IBT/C-25-230/240-E14-25*
------------	--------------------------

Dimensional drawing

Product	D (max)	C (max)
Appliance 25W E14 230-240V T25CL OV 1CT/20F/NO	25 mm	57 mm



APP 25W E14 230-240V T25 CL OV

