



# Deco Tubular

## Deco 10W E14 230-240V T25 CL 1CT/10X10F

Tubular lamps with single- and coiled-coil filaments and clear, inside frosted or internally coated white bulbs with B- or E-base

### Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	34 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	10.0 W
Lamp Current (Nom)	0.04 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230-240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T25 [T 25mm]
Approval and Application	
Energy Consumption kWh/1000 h	10 kWh
Product Data	
Order product name	Deco 10W E14 230-240V T25 CL 1CT/10X10F
Full product name	Deco 10W E14 230-240V T25 CL 1CT/10X10F
Full product code	871150004221750
Order code	924198344440
Material Nr. (12NC)	924198344440
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500042217
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500252142

# Deco Tubular

## Dimensional drawing

Product	D (max)	C (max)
Deco 10W E14 230-240V T25 CL 1CT/10X10F	26 mm	59 mm

