



Halogen High Voltage SE (Film/Studio)

6893P FEP (CP/77) 230V 1000W

The high, constant output and consistent color temperature of these single ended halogen lamps ensure attractive, accurately exposed pictures for both film and video. Furthermore, these lamps incorporate the highly innovative P3 technology, developed by Philips. This allows the lamps to be used at higher temperatures, which extends overall lifetime and consistency of their high-quality light output. P3 technology also allows the lamp to be used in any burning position and enables more compact designs of fixtures. In addition, the very wide choice of dimensions and power ratings opens new levels of creative freedom for the luminaire designer.


Product data

General Information	
Cap-Base	G9.5 [G9.5]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	180 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3200 K
Operating and Electrical	
Power Consumption	1,000 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Product Data	
Order product name	6893P 1000W G9.5 230V 1CT/10
Full product name	6893P FEP (CP/77) 230V 1000W
Full product code	871150018466525
Order code	141077
Material Nr. (12NC)	924400042928
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500184665
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500184672

Halogen High Voltage SE (Film/Studio)

Dimensional drawing



Product	D	H	W	L	C	P	P	R	K	K
	(max)				(max)	(max)	(min)		(max)	(min)
6983P	13/16	15/16	1/4	2-7/16	4-3/16	1/8	1/8	3/8	1/2	3/8
1000W	inch	inch	inch	inch	inch	inch	inch	inch	inch	inch
G9.5										
230V										
1CT/10										

