



# Halogen High Voltage SE (Film/Studio)

## 6638P 650W GY9.5 230V 1CT/10


The high, constant output and consistent color temperature of these single ended halogen lamps ensure attractive, accurately exposed pictures for both film and video. Furthermore, these lamps incorporate the highly innovative P3 technology, developed by Philips. This allows the lamps to be used at higher temperatures, which extends overall lifetime and consistency of their high-quality light output. P3 technology also allows the lamp to be used in any burning position and enables more compact designs of fixtures. In addition, the very wide choice of dimensions and power ratings opens new levels of creative freedom for the luminaire designer.

### Product data

General Information	
Cap-Base	GY9.5 [GY9.5]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	180 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3200 K
Operating and Electrical	
Power Consumption	650 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Product Data	
Order product name	6638P 650W GY9.5 230V 1CT/10
Full product name	6638P 650W GY9.5 230V 1CT/10
Full product code	871150018448125
Order code	18448125
Material Nr. (12NC)	924501342928
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500184481
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500184498

# Halogen High Voltage SE (Film/Studio)

## Dimensional drawing



Product	D (max)	H	W	L	C (max)	R	K (max)	K	K (min)
6638P	22 mm	12	11 mm	46.5	90 mm	9.53	8.6 mm	7.7	7.0 mm
650W GY9.5		mm		mm		mm		mm	
230V 1CT/10									

