



Compact Source

6989P 575W G9.5 115V 1CT/10

The very compact filament in the Compact Source series helps create a proportionately high beam intensity and the Compact Source range is therefore ideal for the latest generation of high-performance luminaires. Also, thanks to their low energy consumption, each dimmer can serve significantly more fixtures, thereby reducing overall dimmer costs. What's more, the Compact Source lamps incorporate the innovative P3 technology, developed by Philips, which enables the lamps to be used at higher temperatures in any burning position. This results in longer lamp lifetimes, reduced lamp replacement costs, and a more consistent lighting performance over the whole lifetime of the lamp.

Product data

General Information	
Cap base	G9.5 [G9.5]
Philips code	6989P
ANSI Code	GLC
Operating position	UNIVERSAL [Any or Universal (U)]
Main application	Entertainment
Life to 50% failures (nom.)	400 h
System description	P3 Technology
Light Technical	
Luminous flux (rated) (nom.)	15500 lm
Correlated colour temperature (nom.)	3200 K
Color rendering index (nom.)	100
Operating and Electrical	
Power (Rated) (Nom)	575 W
Rapid-acting HBC fuse	10 V


Voltage (Nom)	115 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb finish	Clear (CL)
Filament shape	Bi-Plane
Filament dimensions WxH	9.0x8.0
Luminaire Design Requirements	
Pinch temperature (max.)	500 °C
Product Data	
Full product code	871150051854525
Order product name	6989P 575W G9.5 115V 1CT/10
EAN/UPC – product	8711500518545
Order code	51854525

Compact Source

Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	924534234428

Net weight (piece)	0.024 kg
--------------------	----------

Dimensional drawing



6989P 575W G9.5 115V

Product	D (max)	H	W	L	C (max)
6989P 575W G9.5 115V 1CT/10	19 mm	7.5 mm	9 mm	60.5 mm	101 mm

