



# Compact Source

## 6992P 575W G9.5 115V 1CT/10

The very compact filament in the Compact Source series helps create a proportionately high beam intensity and the Compact Source range is therefore ideal for the latest generation of high-performance luminaires. Also, thanks to their low energy consumption, each dimmer can serve significantly more fixtures, thereby reducing overall dimmer costs. What's more, the Compact Source lamps incorporate the innovative P3 technology, developed by Philips, which enables the lamps to be used at higher temperatures in any burning position. This results in longer lamp lifetimes, reduced lamp replacement costs, and a more consistent lighting performance over the whole lifetime of the lamp.

### Product data

General Information	
Cap-Base	G9.5 [G9.5]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	1,200 hour(s)

  

Light Technical	
Correlated Color Temperature (Nom)	3100 K
Color rendering index (CRI)	100

  

Operating and Electrical	
Power Consumption	575 W
Voltage (Nom)	115 V
Voltage (Nom)	115 V

  

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear

  

Product Data	
Full product code	871150051894125
Order product name	6992P 575W G9.5 115V 1CT/10
Order code	924538534428
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	924538534428
Full product name	6992P 575W G9.5 115V 1CT/10
EAN/UPC - Case	8711500520999
EAN/UPC - Product/Case	8711500518941

## Compact Source

### Dimensional drawing

Product	D (max)	H	W	L	C (max)
6992P 575W G9.5 115V 1CT/10	19 mm	9.5 mm	9 mm	60.5 mm	101 mm

