



# Compact Source

## 6982P 230V 800W G9.5 10PK

The very compact filament in the Compact Source series helps create a proportionately high beam intensity and the Compact Source range is therefore ideal for the latest generation of high-performance luminaires. Also, thanks to their low energy consumption, each dimmer can serve significantly more fixtures, thereby reducing overall dimmer costs. What's more, the Compact Source lamps incorporate the innovative P3 technology, developed by Philips, which enables the lamps to be used at higher temperatures in any burning position. This results in longer lamp lifetimes, reduced lamp replacement costs, and a more consistent lighting performance over the whole lifetime of the lamp.


### Product data

General Information	
Cap-Base	G9.5 [G9.5]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	200 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3200 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	800 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Product Data	
Order product name	6982P 800W G9.5 230V 1CT/10
Full product name	6982P 230V 800W G9.5 10PK
Full product code	871150050109725
Order code	134213
Material Nr. (12NC)	924545644228
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500501097
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500501103

Compact Source

Dimensional drawing



Product	D (max)	H	W	L	C (max)
6982P 800W G9.5 230V 1CT/10	13/16 inch	1/2 inch	3/8 inch	2-7/16 inch	4-1/8 inch

