



Hi-Brite

6980Z 1200W G22 80V 10PK

The compact, shock-resistant design of the Hi-Brite lamp series makes it easy to handle and ideal for moving head systems. Also, the compact filament ensures a high beam intensity, which can be used to reduce energy consumption: for example, 1200W can now be used instead of 2500W. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures in any burning position, which further extends lamp lifetime, reduces lamp replacement costs and ensures consistency of high-quality light output.


Product data

General Information	
Cap-Base	G22 [G22]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	200 hour(s)
Light Technical	
Color rendering index (CRI)	-
Operating and Electrical	
Power Consumption	1,200 W
Voltage (Nom)	80 V
Voltage (Nom)	80 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Product Data	
Order product name	6980Z 1200W G22 80V 10PK
Full product name	6980Z 1200W G22 80V 10PK
Full product code	871150051946725
Order code	382960
Material Nr. (12NC)	924546528928
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500519467
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500519498

Hi-Brite

Dimensional drawing



Product	D (max)	H	W	L	C (max)
6980Z 1200W G22 80V 10PK	25 mm	10.2 mm	11.7 mm	63.5 mm	140 mm

