



# Halogen High Voltage SE (Film/Studio)

## 7002Y 240V 1000W G22

The high, constant output and consistent color temperature of these single ended halogen lamps ensure attractive, accurately exposed pictures for both film and video. Furthermore, these lamps incorporate the highly innovative P3 technology, developed by Philips. This allows the lamps to be used at higher temperatures, which extends overall lifetime and consistency of their high-quality light output. P3 technology also allows the lamp to be used in any burning position and enables more compact designs of fixtures. In addition, the very wide choice of dimensions and power ratings opens new levels of creative freedom for the luminaire designer.

### Product data


General Information		Voltage (Nom)		240 V
Base	G22 [ G22]	Controls and Dimming		
Philips Code	7002Y	Dimmable	Yes	
ANSI Code	-	Mechanical and Housing		
LIF Code	-	Bulb Finish	Clear (CL)	
Operating Position	Universal [ Universal]	Filament Shape	Bi-Plane	
Main Application	Entertainment	Filament Dimensions WxH	12.7x16.8	
Life to 50% Failures (Nom)	250 h	Luminaire Design Requirements		
System Description	P3 Technology	Bulb Temperature (Max)	900 °C	
		Pinch Temperature (Max)	500 °C	
Light Technical		Product Data		
Luminous Flux (Rated) (Nom)	29000 lm	Order product name	7002Y 1000W G22 240V 1CT/10	
Correlated Color Temperature (Nom)	3200 K	EAN/UPC - Product	8711500187024	
Operating and Electrical				
Power (Rated) (Nom)	1000 W			
Rapid Acting HBC Fuse	6.3 V			

## Halogen High Voltage SE (Film/Studio)

Order code	156208
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	924553645528

Net Weight (Piece)	0.086 kg
--------------------	----------

### Dimensional drawing



7002Y 1000W G22 240V

Product	D (max)	H	W	L	C (max)	P (max)	P (min)	R	K (max)	K (min)
7002Y	22 mm	13.5	11.5	72.5	140	6.40	6.30	22.22	26.54	24.89
1000W		mm	mm	mm	mm	mm	mm	mm	mm	mm
G22 240V										
1CT/10										

