



HPL

7008 750W HEAT SINK 115V 1CT/10

HPL lamps include a barrel-shaped filament that is approved by ETC for use in its Source Four™ fixtures. Bright, high quality light and high beam intensity is assured by the optimal filament design, while the unique P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which extends lifetime and consistency of high-quality light output, resulting in fewer early failures and fewer maintenance man hour costs.

Product data

General Information	
Cap-Base	HEATSINK [Heat Sink]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	300 hour(s)

Light Technical	
Color rendering index (CRI)	100


Operating and Electrical	
Power Consumption	750 W
Voltage (Nom)	115 V
Voltage (Nom)	115 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear

Product Data	
Order product name	7008 750W Heat Sink 115V 1CT/10
Full product name	7008 750W HEAT SINK 115V 1CT/10
Full product code	871150018537225
Order code	18537225
Material Nr. (12NC)	924555134428
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500185372
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500185488

Dimensional drawing



Product	D (max)	H	W	D1	L	C (max)
7008 750W Heat Sink 115V	19 mm	10.5 mm	6.3 mm	6.3 mm	60.3 mm	104 mm
1CT/10						

