



HPL

7008 750W Heat Sink 240V 1CT/10


HPL lamps include a barrel-shaped filament that is approved by ETC for use in its Source Four™ fixtures. Bright, high quality light and high beam intensity is assured by the optimal filament design, while the unique P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which extends lifetime and consistency of high-quality light output, resulting in fewer early failures and fewer maintenance man hour costs.

Product data

General Information	
Base	HEATSINK [Heat Sink]
Philips Code	7008
Operating Position	Universal [Universal]
Main Application	Entertainment
Life to 50% Failures (Nom)	300 h
System Description	P3 Technology
Light Technical	
Luminous Flux (Rated) (Nom)	19750 lm
Correlated Color Temperature (Nom)	3200 K
Color Rendering Index (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	750 W
Rapid Acting HBC Fuse	6.3 V
Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear (CL)
Cap-Base Information	Heat Sink
Filament Shape	Bi-Plane
Filament Dimensions WxH	8.6x11.5x7.5
Luminaire Design Requirements	
Pinch Temperature (Max)	500 °C
Product Data	
Order product name	7008 750W Heat Sink 240V 1CT/10
EAN/UPC - Product	8711500496591
Order code	273466
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	924555145528
Net Weight (Piece)	0.051 kg

Dimensional drawing



Product	D (max)	H	W	D1	L	C (max)
7008 750W Heat Sink	19 mm	11.5 mm	8.6 mm	7.5 mm	60.3 mm	104 mm
240V 1CT/10						

7008 750W Heat Sink 240V

