



Halogen FastFit

7021G 575W 115V LL FastFit

Halogen FastFit lamps are replaced in seconds - thanks to the specially designed base. The compact filament ensures high beam intensity, while the shock-resistant design allows easy handling and reliable use in moving head systems. In addition, the highly innovative P3 technology allows use at higher temperatures, which further extends lifetime and consistency of light output. P3 technology also allows the lamp to be used in any burning position and enables more compact designs of fixtures. And because the FastFit design is also applied to Philips MSR/MSD Gold™ lamps, switching lamp technologies is also quick and easy.

Product data


General Information	
Base	PGJX50 [PGJX50]
Philips Code	7021G
ANSI Code	NPA
Operating Position	Universal [Universal]
Main Application	Entertainment
Life to 50% Failures (Nom)	1500 h
System Description	P3 Technology
Light Technical	
Luminous Flux (Rated) (Nom)	12400 lm
Correlated Color Temperature (Nom)	3000 K
Operating and Electrical	
Power (Rated) (Nom)	575 W
Rapid Acting HBC Fuse	6.3 V
Voltage (Nom)	115 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear (CL)
Filament Shape	Bi-Plane
Filament Dimensions WxH	9 X 9.5
Luminaire Design Requirements	
Pinch Temperature (Max)	480 °C

Product Data	
Order product name	7021G 575W 115V LL FastFit
EAN/UPC - Product	8727900938845
Order code	271668
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	924582834428
Net Weight (Piece)	0.130 kg

Halogen FastFit

Dimensional drawing



Product	D (max)	H	W	L	C (max)	E (max)
7021G 575W 115V LL FastFit	19 mm	9.5 mm	9 mm	79 mm	140 mm	41 mm

7021G 575W PGJX50 115V LL FastFit

