



# Halogen FastFit

## 7021G 575W 115V LL FastFit

Halogen FastFit lamps are replaced in seconds – thanks to the specially designed base. The compact filament ensures high beam intensity, while the shock-resistant design allows easy handling and reliable use in moving head systems. In addition, the highly innovative P3 technology allows use at higher temperatures, which further extends lifetime and consistency of light output. P3 technology also allows the lamp to be used in any burning position and enables more compact designs of fixtures. And because the FastFit design is also applied to Philips MSR/MSD Gold™ lamps, switching lamp technologies is also quick and easy.


### Product data

| General Information                |                                  |
|------------------------------------|----------------------------------|
| Cap-Base                           | PGJX50 [PGJX50]                  |
| Operating Position                 | UNIVERSAL [Any or Universal (U)] |
| Life to 50% Failures (Nom)         | 1,500 hour(s)                    |
| Light Technical                    |                                  |
| Correlated Color Temperature (Nom) | 3000 K                           |
| Operating and Electrical           |                                  |
| Power Consumption                  | 575 W                            |
| Voltage (Nom)                      | 115 V                            |
| Voltage (Nom)                      | 115 V                            |
| Controls and Dimming               |                                  |
| Dimmable                           | Yes                              |

| Mechanical and Housing          |                            |
|---------------------------------|----------------------------|
| Bulb Finish                     | Clear                      |
| Product Data                    |                            |
| Order product name              | 7021G 575W 115V LL FastFit |
| Full product name               | 7021G 575W 115V LL FastFit |
| Full product code               | 872790093884500            |
| Order code                      | 271668                     |
| Material Nr. (12NC)             | 924582834428               |
| Numerator - Quantity Per Pack   | 1                          |
| EAN/UPC - Product/Case          | 8727900938845              |
| Numerator - Packs per outer box | 10                         |
| EAN/UPC - Case                  | 8727900938852              |

# Halogen FastFit

## Dimensional drawing



| Product                    | D (max) | H      | W    | L     | C (max) | E (max) |
|----------------------------|---------|--------|------|-------|---------|---------|
| 7021G 575W 115V LL FastFit | 19 mm   | 9.5 mm | 9 mm | 79 mm | 140 mm  | 41 mm   |

