



Halogen FastFit

7021G 575W 115V LL FastFit

Halogen FastFit lamps are replaced in seconds – thanks to the specially designed base. The compact filament ensures high beam intensity, while the shock-resistant design allows easy handling and reliable use in moving head systems. In addition, the highly innovative P3 technology allows use at higher temperatures, which further extends lifetime and consistency of light output. P3 technology also allows the lamp to be used in any burning position and enables more compact designs of fixtures. And because the FastFit design is also applied to Philips MSR/MSD Gold™ lamps, switching lamp technologies is also quick and easy.


Product data

General Information	
Cap-Base	PGJX50 [PGJX50]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	1,500 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3000 K
Operating and Electrical	
Power Consumption	575 W
Voltage (Nom)	115 V
Voltage (Nom)	115 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Product Data	
Full product code	872790093884500
Order product name	7021G 575W 115V LL FastFit
Order code	924582834428
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	924582834428
Full product name	7021G 575W 115V LL FastFit
EAN/UPC - Case	8727900938852
EAN/UPC - Product/Case	8727900938845

Halogen FastFit

Dimensional drawing



Product	D (max)	H	W	L	C (max)	E (max)
7021G 575W 115V LL FastFit	19 mm	9.5 mm	9 mm	79 mm	140 mm	41 mm

