



HalogenA PAR30S

HalogenA PAR30S 75W E27 230V 30D 1CT/15

Mains-voltage halogen reflector that is easy to install instead of conventional reflector lamps, putting your objects in a superior-quality spot light. Provides crisp halogen light over a long lifetime.

Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Beam Angle (Nom)	30 degree(s)
Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	725 lm

Operating and Electrical	
Power Consumption	75.0 W
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	PAR30S [PAR 3.75 inch/95mm Short]

Approval and Application	
Energy Consumption kWh/1000 h	75 kWh


Product Data	
Order product name	HalogenA PAR30S 75W E27 230V 30D 1CT/15
Full product name	HalogenA PAR30S 75W E27 230V 30D 1CT/15
Full product code	871150050439520
Order code	924710844204
Material Nr. (12NC)	924710844204
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500504395
Numerator - Packs per outer box	15
EAN/UPC - Case	8711500505149

HalogenA PAR30S

Dimensional drawing

Product	D (max)	C (max)
HalogenA PAR30S 75W E27 230V 30D 1CT/15	96 mm	99 mm

Photometric data



Light Distribution Diagram - HalogenA PAR30S 75W E27 230V 30D 1CT/15

