



# Essential MV MR16 Alu

## Ess MV MR16 Alu 50W 120-130V 40D 1CT


The Essential MV MR16 Alu is part of the Philips "Value for Money" ranges. It is ideal for professional end-users looking for accent light - without a transformer - to create contrast in shops, hotels and restaurants.

### Product data

General Information	
Cap-Base	GZ10 [GZ10]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	40 degree(s)
Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	50 W
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Voltage (Nom)	120-130 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	MR16 [2inch/50mm]
Product Data	
Order product name	Ess MV MR16 Alu 50W 120-130V 40D 1CT
Full product name	Ess MV MR16 Alu 50W 120-130V 40D 1CT
Full product code	871150088792400
Order code	924712536183
Material Nr. (12NC)	924712536183
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500887924
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500887955

# Essential MV MR16 Alu

## Dimensional drawing



Product	D (max)	C (max)
Ess MV MR16 Alu 50W 120-130V 40D 1CT	50.7 mm	47.5 mm

