



Double Ended Linear

Double Ended Linear 500T3Q/CL120V 12PK

High-quality white light with superior lumen performance Halogen Double Ended lamps provide bright, white light for work lights and security lighting. Rugged construction for busy work sites. Offered in several lengths to meet most application needs. High lumen output provides light where you need it.

Product data

General Information		Approval and Application		
Base	R7S [R7s]	Energy Efficiency Label (EEL)	D	
Operating Position	Universal [Universal]	Luminaire Design Requirements		
Nominal Lifetime (Nom)	2000 h	Bulb Temperature (Max)	900 °C	
Light Technical		Pinch Temperature (Max)	350 °C	
Initial lumen (Nom)	9500 lm	Product Data		
Correlated Color Temperature (Nom)	2900 K	Order product name	Double Ended Linear PLUS PRO S 500W R7s 120V 1CT/12	
Luminous Efficacy (rated) (Nom)	19.0 lm/W	EAN/UPC - Product	046677100100	
Color Rendering Index (Nom)	100	Order code	200105	
Operating and Electrical		Numerator - Quantity Per Pack	1	
Power (Rated) (Nom)	500 W	Numerator - Packs per outer box	12	
Lamp Current (Nom)	4.17 A	Material Nr. (12NC)	924735334593	
Starting Time (Nom)	0.0 s	Net Weight (Piece)	0.010 kg	
Voltage (Nom)	120 V	Controls and Dimming		
Controls and Dimming		Dimmable	Yes	
Mechanical and Housing		Mechanical and Housing		
Bulb Finish	Clear	Bulb Finish		Clear

Double Ended Linear

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Double Ended Linear PLUS	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm
PRO S 500W R7s 120V ICT/12					

DESmall 500W R7s 120V

