



Plusline Small

PLUS PRO S 500W R7s 230V T3 CL 1BC

Mains-voltage linear lamp giving white halogen light

Product data

| General Information | |
|------------------------|----------------------------------|
| Cap-Base | R7S [R7s] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 2.000 hour(s) |
| Rated Lifetime (Hours) | 2.000 hour(s) |
| Lighting Technology | Halogen |

| Light Technical | |
|------------------------------------|-----------|
| Luminous Flux | 9.660 lm |
| Correlated Color Temperature (Nom) | 2900 K |
| Luminous Efficacy (rated) (Nom) | 19.3 lm/W |
| Color rendering index (CRI) | 100 |

| Operating and Electrical | |
|--------------------------|--------|
| Power Consumption | 500 W |
| Lamp Current (Nom) | 2.17 A |
| Starting Time (Nom) | 0.0 s |
| Voltage (Nom) | 230 V |
| Voltage (Nom) | 230 V |


| Controls and Dimming | |
|----------------------|-----|
| Dimmable | Yes |

| Mechanical and Housing | |
|------------------------|------------------|
| Bulb Finish | Clear |
| Bulb Shape | T3 [T 12mm (T3)] |

| Product Data | |
|---------------------------------|------------------------------------|
| Order product name | PLUS PRO S 500W R7s 230V T3 CL 1BC |
| Full product name | PLUS PRO S 500W R7s 230V T3 CL 1BC |
| Full product code | 871150049831101 |
| Order code | 924735544280 |
| Material Nr. (12NC) | 924735544280 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500498311 |
| Numerator - Packs per outer box | 100 |
| EAN/UPC - Case | 8711500865588 |

Plusline Small

Dimensional drawing



| Product | D (max) | B (max) | B | B (min) | C (max) |
|---------------------------------------|---------|----------|----------|----------|----------|
| PLUS PRO S 500W R7s 230V T3 CL 1BC | 12 mm | 115.8 mm | 114.2 mm | 112.6 mm | 117.6 mm |

