



# Plusline Small

## Plusline S 200W R7s 230V 1CT/10X10F

Mains-voltage linear lamp giving white halogen light


### Product data

| Informasi Umum                  |                                       |
|---------------------------------|---------------------------------------|
| Tutup-Dasar                     | R7S [R7s]                             |
| Posisi Pengoperasian            | UNIVERSAL [Setiap atau Universal (U)] |
| Nominal masa pakai              | 2.000 jam                             |
| Nilai Masa Pakai (Jam)          | 2.000 jam                             |
| Teknologi Pencahayaan           | Halogen                               |
| Teknis Lampu                    |                                       |
| Flux Cahaya                     | 3.000 lm                              |
| Suhu Warna Terkorelasi (Nom)    | 2900 K                                |
| Daya Penerangan (terukur) (Nom) | 15 lm/W                               |
| Indeks renderasi warna (CRI)    | 100                                   |
| Pengoperasian dan Kelistrikan   |                                       |
| Konsumsi Daya                   | 200 W                                 |
| Arus Lampu (Nom)                | 0,87 A                                |
| Waktu Mulai (Nom)               | 0,0 s                                 |
| Tegangan (Nom)                  | 230 V                                 |
| Tegangan (Nom)                  | 230 V                                 |

| Kontrol dan Peredupan                 |                                     |
|---------------------------------------|-------------------------------------|
| Dapat diredupkan                      | Ya                                  |
| Mekanis dan Housing                   |                                     |
| Lapisan bohlam                        | Bening                              |
| Bentuk Bohlam                         | T3 [T 12mm (T3)]                    |
| Data Produk                           |                                     |
| Nama produk pesanan                   | Plusline S 200W R7s 230V 1CT/10X10F |
| Nama lengkap produk                   | Plusline S 200W R7s 230V 1CT/10X10F |
| Kode produk lengkap                   | 872790080909100                     |
| Kode urutan                           | 924735744201                        |
| No. Material (12NC)                   | 924735744201                        |
| Numerator - Jumlah Per Pak            | 1                                   |
| EAN/UPC - Produk/Kantung              | 8727900809091                       |
| Numerator - Pak per kotak bagian luar | 100                                 |
| EAN/UPC - Kantung                     | 8727900809107                       |

Plusline Small

Dimensional drawing



| Product                                 | D (max) | B (max)  | B        | B (min)  | C (max)  |
|-----------------------------------------|---------|----------|----------|----------|----------|
| Plusline S 200W R7s 230V 1CT/<br>10X10F | 12 mm   | 115,8 mm | 114,2 mm | 112,6 mm | 117,6 mm |

