



Plusline Small

Plusline S 200W R7s 240V 1BC/10

Mains-voltage linear lamp giving white halogen light

Product data

| General Information | |
|------------------------------------|----------------------------------|
| Cap-Base | R7S [R7s] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 2,000 hour(s) |
| Rated Lifetime (Hours) | 2,000 hour(s) |
| Lighting Technology | Halogen |
| Light Technical | |
| Luminous Flux | 3,000 lm |
| Correlated Color Temperature (Nom) | 2900 K |
| Luminous Efficacy (rated) (Nom) | 15 lm/W |
| Color rendering index (CRI) | 100 |
| Operating and Electrical | |
| Power Consumption | 200 W |
| Lamp Current (Nom) | 0.83 A |
| Starting Time (Nom) | 0.0 s |
| Voltage (Nom) | 240 V |
| Voltage (Nom) | 240 V |

| Controls and Dimming | |
|---------------------------------|---------------------------------|
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Finish | Clear |
| Bulb Shape | T3 [T 12mm (T3)] |
| Product Data | |
| Order product name | Plusline S 200W R7s 240V 1BC/10 |
| Full product name | Plusline S 200W R7s 240V 1BC/10 |
| Full product code | 872790081920500 |
| Order code | 924735745597 |
| Material Nr. (12NC) | 924735745597 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8727900819205 |
| Numerator - Packs per outer box | 10 |
| EAN/UPC - Case | 8727900819212 |

Plusline Small

Dimensional drawing



| Product | D (max) | B (max) | B | B (min) | C (max) |
|---------------------------------|---------|----------|----------|----------|----------|
| Plusline S 200W R7s 240V 1BC/10 | 12 mm | 115.8 mm | 114.2 mm | 112.6 mm | 117.6 mm |

