



PAR16

45PAR16/HAL/FL27 120V 15PK

Philips Halogen PAR lamps will provide bright, white light across the product line and feature excellent beam qualities for accent or ambient lighting. Their optimized coil and burner design allows for clear, crisp lighting effects with excellent color rendering, making it easy to optimize the look and feel of your store and your merchandise.


Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	3,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	27 degree(s)
Luminous Flux	420 lm
Luminous Intensity (Nom)	1,250 cd
Correlated Color Temperature (Nom)	2900 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	45 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Reflector Finish	Aluminized
Bulb Shape	PAR16 [PAR 2 inch/50mm]
Product Data	
Order product name	45PAR16/HAL/FL27 120V 15PK
Full product name	45PAR16/HAL/FL27 120V 15PK
Order code	924757104904
Material Nr. (12NC)	924757104904
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677263454
Numerator - Packs per outer box	15
EAN/UPC - Case	50046677263459

PAR16

Dimensional drawing



Product

45PAR16/HAL/FL27 120V 15PK

