



# Long Life IR PAR30S

## Long Life IR 50PAR30L/IRC+/WFL40 120V 15/1

Optically advanced Halogen PAR lamps are designed with innovative technologies that provide superior light performance while reducing operating costs.

### Product data


General Information	
Base	E26 [ Single Contact Medium Screw]
Operating Position	Universal [ Universal]
Main Application	Accent & Downlighting
Gas Filling	GAS
Life with 3 Hour Per Day Use	3.8 a
Light Technical	
Beam Angle (Nom)	40 °
Initial lumen (Nom)	900 lm
Luminous Intensity (Nom)	1550 cd
Beam Description	Wide Flood [ Wide Flood]
Correlated Color Temperature (Nom)	2750 K
Color Rendering Index (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	50 W
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Clear (CL)

Cap-Base Information	Brass [ Brass Cap]
Bulb Material	Hard Glass
Reflector Finish	Aluminized
Filament Shape	CC-8 [ Axial]
Approval and Application	
Estimated Energy Cost Per Year	6.02 \$
Product Data	
Order product name	Long Life IR 50PAR30L/IRC+/WFL40 120V 15/1
EAN/UPC - Product	046677238001
Order code	238006
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	15
Material Nr. (12NC)	924757141301
Net Weight (Piece)	210.000 g

# Long Life IR PAR30S

## Dimensional drawing

Product	D	C (max)
Long Life IR 50PAR30L/IRC+/WFL40 120V 15/1	3.75 in	4.5 in



PAR30 IRC 50W E26/BRC 120V WFL 40D CC-8

