



# D.C. Bayonet

## 100Q/CL/DC ESR 120V 12PK

Accent lighting with improved lumens and higher performance Halogen DC Bayonett Capsule lamps provide bright, white light for decorative and accent lighting and general illumination. Offered in T4 bulb size with DC Bayonette base configurations. These lamps offer a rated average life ranging from 1000 to 2000 hours depending upon the product. \*\* Rated average life is the length of operation (in hours) at which point an average of 50% of the lamps will still be operational and 50% will not.

### Product data

General Information	
Base	BA15D [ BA15d]
Operating Position	Universal [ Universal]
Main Application	General Lighting (G)
Gas Filling	GAS
Light Technical	
Initial lumen (Nom)	1900 lm
Correlated Color Temperature (Nom)	2700 K
Color Rendering Index (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	100 W
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Clear (CL)


Cap-Base Information	Aluminium [ Aluminium Cap]
Bulb Material	Standard Quartz
Filament Shape	CC-8 [ Axial]
Product Data	
Order product name	DCBAY 100W 120V ESR 1CT/12
EAN/UPC - Product	046677115074
Order code	442780
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	924794736381
Net Weight (Piece)	0.009 kg

## D.C. Bayonet

### Dimensional drawing

#### Product

DCBAY 100W 120V ESR 1CT/12



DC-BAY 100W 120V T4 Std-Q CL

