



Halogen Low Voltage

13163 ELC/5H 250W GX5.3 24V 1CT/24


The long lifetime of most of the Halogen Low Voltage lamps is further extended by the unique P3 technology developed by Philips. This allows the lamp to be used at higher temperatures, thereby extending the lamp's lifetime, reducing early failures, and resulting in fewer maintenance man hour costs. P3 also ensures consistency of high-quality light output, and allows the lamp to be used in any burning position, which enables more compact fixture designs. In addition, the compact filament produces a clean white light and high beam intensity for true natural colors on stage and without any hotspots.

Product data

General Information		Reflector Finish	
Cap-Base	GX5.3	Smooth	
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]	Bulb Shape	
Life to 50% Failures (Nom)	500 hour(s)	R50	
Light Technical		Product Data	
Color rendering index (CRI)	100	Order product name	13163 ELC/5H 250W GX5.3 24V 1CT/24
Operating and Electrical		Full product name	13163 ELC/5H 250W GX5.3 24V 1CT/24
Power Consumption	250 W	Full product code	871150041347530
Voltage (Nom)	24 V	Order code	924862720540
Voltage (Nom)	24 V	Material Nr. (12NC)	924862720540
Controls and Dimming		Numerator - Quantity Per Pack	1
Dimmable	Yes	EAN/UPC - Product/Case	8711500413475
Mechanical and Housing		Numerator - Packs per outer box	24
Bulb Material	Quartz-UV Open	EAN/UPC - Case	8711500435736

Halogen Low Voltage

Dimensional drawing



Product	D (max)	C (max)
13163 ELC/5H 250W GX5.3 24V 1CT/24	50 mm	44.5 mm

