



Halogen Low Voltage

13163 ELC/5H 250W GX5.3 24V 1CT/24

The long lifetime of most of the Halogen Low Voltage lamps is further extended by the unique P3 technology developed by Philips. This allows the lamp to be used at higher temperatures, thereby extending the lamp's lifetime, reducing early failures, and resulting in fewer maintenance man hour costs. P3 also ensures consistency of high-quality light output, and allows the lamp to be used in any burning position, which enables more compact fixture designs. In addition, the compact filament produces a clean white light and high beam intensity for true natural colors on stage and without any hotspots.

Product data

General Information	
Cap-Base	GX5.3 [GX5.3]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	500 hour(s)
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	250 W
Voltage (Nom)	24 V
Voltage (Nom)	24 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Material	Quartz-UV Open

Reflector Finish	Smooth
Bulb Shape	R50 [R 50mm]
Product Data	
Order product name	13163 ELC/5H 250W GX5.3 24V 1CT/24
Full product name	13163 ELC/5H 250W GX5.3 24V 1CT/24
Full product code	871150041347530
Order code	924862720540
Material Nr. (12NC)	924862720540
Local order code	ELC5H
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500413475
Numerator - Packs per outer box	24
EAN/UPC - Case	8711500435736

Halogen Low Voltage

Dimensional drawing



Product	D (max)	C (max)
13163 ELC/5H 250W GX5.3 24V 1CT/24	50 mm	44.5 mm

