



Double Ended Linear

Double Ended Linear BC100T3Q/CL 12/1

High-quality white light with superior lumen performance Halogen Double Ended lamps provide bright, white light for work lights and security lighting. Rugged construction for busy work sites. Offered in several lengths to meet most application needs. High lumen output provides light where you need it.

Product data

General Information	
Base	R7S [R7s]
Operating Position	Universal [Universal]
Nominal Lifetime (Nom)	2000 h

Light Technical	
Initial lumen (Nom)	1400 lm
Correlated Color Temperature (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	14 lm/W
Color Rendering Index (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	100 W
Lamp Current (Nom)	0.83 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	120 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear

Cap-Base Information	na [-]
----------------------	---------


Approval and Application	
Energy Efficiency Label (EEL)	E

Luminaire Design Requirements	
Bulb Temperature (Max)	900 °C
Pinch Temperature (Max)	350 °C

Product Data	
Order product name	Double Ended Linear BC100T3Q/CL 12/1
EAN/UPC - Product	046677415600
Order code	415604
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	924884636301
Net Weight (Piece)	0.006 kg

Double Ended Linear

Dimensional drawing



DEComp 100W R7s 120V T3 CL

Product	D (max)	B (max)	B	B (min)	C (max)
Double Ended Linear BC100T3Q/CL 12/1	12 mm	76.5 mm	74.9 mm	73.3 mm	78.3 mm

