



# Twistline GU10

## BC35 TWISTLINE GU10/FL25 TP

Bright, white accent light with superior energy savings Philips Twistline GU10 Philips Halogen Twistline MR16 with GU10 base provide bright white accent light. The twist and lock base enables easy installation and a secure fit. Suited for track and recessed lighting applications.

### Product data

General Information	
Base	GU10 [ GU10]
Operating Position	Universal [ Universal]
Nominal Lifetime (Nom)	2000 h
Light Technical	
Beam Angle (Nom)	20 °
Luminous Intensity (Max)	800 cd
Correlated Color Temperature (Nom)	2800 K
Color Rendering Index (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	35 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	120 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Product Data	
Order product name	BC35 TWISTLINE GU10/FL25 TP
EAN/UPC - Product	046677415730
Order code	415737
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	924887136384
Net Weight (Piece)	0.046 kg

## Twistline GU10

### Dimensional drawing



Product	D (max)	C (max)
BC35 TWISTLINE GU10/FL25 TP	50.7 mm	53 mm

TWIST 35W GU10 120V 20D

