



MR16

BC20MRC16/FL36 6/3

Philips Halogen MR16 lamps provide a bright white light for accent lighting. They make it easy to optimize the look and feel of your brand, your merchandise, and the shoppers experience, with lower operating costs.


Product data

General Information	
Cap-Base	GU5.3
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	3,000 hour(s)
Switching Cycle	12,000
Rated Lifetime (Hours)	3,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	36 degree(s)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	205 lm
Operating and Electrical	
Power Consumption	20.0 W
Lamp Current (Nom)	1.67 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	12 V
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16
Approval and Application	
Energy Consumption kWh/1000 h	21 kWh
Product Data	
Order product name	BC20MRC16/FL36 6/3
Full product name	BC20MRC16/FL36 6/3
Order code	924888217101
Material Nr. (12NC)	924888217101
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677415686
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677415681

MR16

Dimensional drawing



Product	D (max)	C (max)
BC20MRC16/FL36 6/3	50.7 mm	46 mm

