



# MR16

## BC50MRC16/SP10 EXT 12/1 TP

Philips Halogen MR16 lamps provide a bright white light for accent lighting. They make it easy to optimize the look and feel of your brand, your merchandise, and the shoppers experience, with lower operating costs.


### Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	3,000 hour(s)
Rated Lifetime (Hours)	3,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	10 degree(s)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	50 W
Lamp Current (Nom)	4.17 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	12 V
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Product Data	
Order product name	BC50MRC16/SP10 EXT 12/1 TP
Full product name	BC50MRC16/SP10 EXT 12/1 TP
Order code	924888717101
Material Nr. (12NC)	924888717101
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677415631
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677415636

MR16

Dimensional drawing



Product	D (max)	C (max)
BC50MRC16/SP10 EXT 12/1 TP	51 mm	46 mm

