



Capsuleline

Hal-Caps 2y 20W G4 12V CL 2BS/10

Low-voltage halogen capsule. Ideal solution for small decorative luminaires. UV-block glass and low-pressure filling allow usage without cover glass. The compact Capsuleline delivers crisp white light over a long lifetime.

Product data

| General Information | |
|------------------------------------|----------------------------------|
| Cap-Base | G4 [G4] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 2,000 hour(s) |
| Switching Cycle | 8,000 |
| Rated Lifetime (Hours) | 2,000 hour(s) |
| Lighting Technology | Halogen |
| Light Technical | |
| Luminous Flux | 255 lm |
| Correlated Color Temperature (Nom) | 2800 K |
| Luminous Efficacy (rated) (Nom) | 12.5 lm/W |
| Color rendering index (CRI) | 100 |
| Operating and Electrical | |
| Power Consumption | 20.0 W |
| Lamp Current (Nom) | 1.67 A |
| Starting Time (Nom) | 0.0 s |
| Warm-up time to 60% light | instant full light s |
| Power Factor (Fraction) | 1 |
| Voltage (Nom) | 12 V |
| Voltage (Nom) | 12 V |

| Controls and Dimming | |
|---------------------------------|----------------------------------|
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Finish | Clear |
| Bulb Shape | T9 [T 9mm (T9)] |
| Approval and Application | |
| Energy Consumption kWh/1000 h | 21 kWh |
| Product Data | |
| Order product name | Hal-Caps 2y 20W G4 12V CL 2BS/10 |
| Full product name | Hal-Caps 2y 20W G4 12V CL 2BS/10 |
| Full product code | 872790020306625 |
| Order code | 924892017101 |
| Material Nr. (12NC) | 924892017101 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8727900203066 |
| Numerator - Packs per outer box | 10 |
| EAN/UPC - Case | 8727900204179 |

Dimensional drawing



| Product | D (max) | L | C (max) |
|----------------------------------|---------|-------|---------|
| Hal-Caps 2y 20W G4 12V CL 2BS/10 | 10 mm | 22 mm | 33 mm |

