



Capsuleline

Capsuleline 50W GY6.35 12V CL 2000h 1CT/10X10F


Low-voltage halogen capsule. Ideal solution for small decorative luminaires. UV-block glass and low-pressure filling allow usage without cover glass. The compact Capsuleline delivers crisp white light over a long lifetime.

Product data

General Information	
Cap-Base	GY6.35 [GY6.35]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	850 lm
Correlated Color Temperature (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	17 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	50.0 W
Lamp Current (Nom)	4.17 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	12 V
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T11 [T 11mm]
Approval and Application	
Energy Consumption kWh/1000 h	53 kWh
Product Data	
Order product name	Caps 50W GY6.35 12V CL 2000h 1CT/10X10F
Full product name	Capsuleline 50W GY6.35 12V CL 2000h 1CT/10X10F
Full product code	871150041295950
Order code	41295950
Material Nr. (12NC)	924892217108
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500412959
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500425829

Dimensional drawing



Product	D (max)	L	C (max)
Caps 50W GY6.35 12V CL 2000h 1CT/10X10F	12 mm	30 mm	44 mm

